

## Handle Clamp

**Kumwell** handle clamp has only 3 type differences; HCB00, HCC00 and HCD00, which is adequate to assort with many different sizes and types of graphite mould.



### HCB00

HCB00 type handle clamp assorting with 2"x2" sized mould



### HCC00 and HCD00

HCC00 type handle clamp assorting with 3-1/8" x 3-1/8" sized mould and 2-5/16" distance between prongs.

HCD00 type handle clamp assorting with 4"x4" sized mould and 3" distance between prongs.



### HCB00-XB or HCB00-XB-12D

Handle clamp with chain support for cathodic mould HCB00-XB is used to hold a mould fit at its horizontal and vertical position on up to 4" pipe's diameter and HCB00-XB-12D special chain support for 5" to 12" pipe's diameter.



### HCC00-X or HCD00-X

Handle clamp with chain support "X"

It is used to hold a mould fit at its horizontal and vertical position on up to 4" pipe's diameter.

Special chain support can be requested.

HCC00-X and HCD00-X suit to collaborate with CRE6P, CRE18P, CRE19P, CRE20P, CP1 mould's types.

**Note :** Special requirement can be requested.